

# Nivå och Flödesutrustning -

# **Digiflow 515**

(Microprocessor Gas and Steam Flow Computer - Consumption and Enthalpy for Steam)



# **Product Functions**

- Indication of Flow Rate and Total of Volume, Mass and Energy.
- Temperature and Pressure Compensation.
- Input Signals 4-20 mA analog or frequency for flow input.
- Dual Ranged D.P. Transmitter Inputs
- Simplified Programming.
- User Menus in Three Languages.
- Control of a Sensor-purge-unit.
- Data Logging Output.



#### 1 Functions

- Indication of flow rate and total of volume, mass and energy
- Temperature and pressure compensation
- Input signals 4...20 mA analogue or frequency for flow input
- Dual ranged \Deltap-transmitter inputs
- Simple programming
- User menus in three languages
- Control of a sensor-purge-unit
- Data logging output

The DigiFlow 515 combines compensation for gas and vapors to the following equations:

- 1. Ideal Gas: Temperature and pressure correction; compressibility correction not required.
- General Gas: Temperature and pressure correction with compressibility correction calculated using the Redlich-Kwong state equation. This equation is suitable for gases with known properties. Information about common industrial gases are provided in the operating manual.
- Natural Gas: Compressibility is calculated using the AGA-NX-19-mod equation for natural gases of low gross caloric value.
- Steam Flow Computer. Based on the IFC 1967. Mass flow correction of the flowing steam using pressure and temperature.
- 5. Energy: The heat quantity is calculated based on enthalpy and mass flow.(for steam)
- Energy Balance: Assuming a mass balance in upstream-and downstream pipe, an energy balance of the loop is calculated. (for steam in upstream)

Inputs from several flow meters are accepted. Examples of these sensors are (VORTEX), turbine, orifice plate, averaging pitot tubes like (ITABAR-Flow sensor), wedges and target flow meters. To increase the measured flow range of an ITABAR-Flow sensor, it is possible to use two differential pressure transmitters whose ranges overlap with automatic crossover in the computer.

The backlit two rows alphanumeric display shows the instantaneous readings of Flow or Totals, and the four key touchpad it is used to program and configure the unit.

All **DigiFlow 515's** are equipped with 4 analog inputs 4 – 20mA, 2 frequency inputs and 2 Pt100– inputs for RTD according to DIN 43760 in 2–,3– or 4–wire connection.

A scalable Pulse Output to drive external counters, 2 Relay Outputs for Low/High-Flow alarms and an RS232 interface are also standard features of the **DigiFlow 515**.

Optionally there are up to two scaleable Analog Outputs available.

There is also a capability to control an Sensor Purge Unit for automatic purge control in hazardous environments.

The Pulse Output, and the Alarm Outputs will operate proportionally to the mass, corrected volume or energy depending on which value will be displayed as Standard Display.

The Analog Output can be assigned to one of measured or calculated values, shown on the display.

The RS232/RS485 Interface will output all parameters which are displayed. This can be done to a printer or a host computer.

An integrated real time clock is included to send protocols in selectable intervals, up to 9999min. Accumulated totals may be reset.

The Totals can be reset by pressing the related key on the keyboard or by a voltage input at the related rear-terminal jack.

The **DigiFlow 515** is powered by AC of 115/230 VAC 50/60 Hz. Optionally voltages between 24 and 28 V AC/DC.

The **DigiFlow 515** provides an adjustable voltage of 18V DC for powering sensors. Maximum current is 100mA.



# 2 Flow Meter Inputs

Most types of flow meters can be used in conjunction with the DigiFlow 515. Including:

- 1. Linear frequency producing flow meters like (VORTEX), turbines or positive displacement.
- Non–linear frequency producing flow meters. A 12 point correction curve can be programmed to linearize the signal.
- Volumetric flow meters with outputs of 4 20mA such as (VORTEX) or turbine meters with a frequency to current converter on the output.
- Differential Pressure devices for ITABAR-sensors or orifice plates, where a square law relationship applies.
- 5. Linear Differential Pressure devices where the 4 20mA output is proportional to the flow rate.
- Dual Range Differential Pressure devices where two separately spanned transmitters are used across a common flow device (ITABAR-sensor).

*Non–linear Differential Pressure devices* like laminar flow tubes. A 12 point correction curve can be programmed to linearize the signal.

### **3 Displayed Parameters**

During operation the display shows information which is selected by pressing the SCAN-key. After one minute, without any key press, the display will return to the selected standard display.

| Standard display |                                       | Flow rate of the mass, corrected volume or energy is displayed in<br>units per day, hour, minute or second.<br>By pressing the TOTAL-key the display changes to show the<br>accumulated totals of mass, volume or energy. These counters can<br>be reset by pressing the RESET-key if allowed. |
|------------------|---------------------------------------|--|
| Gas flow         | · · · · · · · · · · · · · · · · · · · | Corrected volume (m <sup>s</sup> or SCF)<br>Mass (kg or lbs)<br>Temperature and pressure (°C or °F, kPa or psi)<br>Compressibility [except ideal gas]<br>Date and time   |
| Steam flow       |                                       | Energy (MJ or BTU)   |



# 4 Technical data

# General:

| Display                               | : backlit, alpha-numeric LC-display, 2 rows, 16 cols, 0.276" char. Height                |
|---------------------------------------|--|
| Keyboard                              | : sealed membrane keyboard with four keys  |
| Transmitter supply                    | : 18 V/100 mA, adjustable via keyboard, isolated   |
| Power                                 | 115/230 V AC; 50/60 Hz, internally switchable  |
|                                       | option: 2428 V AC/DC   |
|                                       |  |
|                                       | power consumption: 10 W @ 230 V AC   |
| 0                                     | without options  |
| Operating temperature                 | : 055 °C (32131 °F)  |
| Housing                               | : enclosure: glass-fiber-reinforced plastic material;                                    |
|                                       | front: aluminium keyboard  |
| Face                                  | : watertight to IP54   |
| Dimensions                            | : 144 mm (B) x 72 mm (H) x 130 mm (T)  |
| Panel cut-out                         | : 137 mm (B) x 67 mm (H)   |
|                                       |  |
| Programming and con                   | figuration:  |
|                                       |  |
| Handheld                              | : No handheld terminal needed. All necessary constants and parameters                    |
|                                       | can be programmed using the keypad.  |
| Language                              | : German, English or French selectable   |
| Languago                              |  |
| Frequency input:                      |  |
| requercy input                        |  |
| Eroquoney rango                       | · 0.25 10 kHz Input 1  |
| Frequency range                       |  |
| In much a inclusion                   | 0,25500 Hz Input 2   |
| Input circuits                        | <ul> <li>Most AC, logic and proximity switches accepted. 0,550 V<sub>PP</sub></li> </ul> |
| Non-linear correction                 | : Up to 12 points for curve fit  |
| Analogue input 4 00                   | m A :  |
| Analogue input 420                    | <u>MA.</u>   |
| Inputo                                | : 2 for flow (colit range), 1 for processing and 1 for temporature or                    |
| Inputs                                | 2 for flow (split range), 1 for pressure and 1 for temperature or                        |
|                                       | 2 for flow (split range) and 2 for pressure for energy-balance.                          |
| Input impedance                       | : 120 Ω  |
| Circuit                               | : All inputs are isolated, no common ground  |
|                                       |  |
| RTD-input:                            |  |
|                                       |  |
| Range                                 | : -190+800 °C [-310+1472 °F]   |
| RTD type                              | : Pt100 acc. to DIN 43760  |
| Non-linear correction                 | : The non-linearity of the RTD is internally compensated.                                |
| Horr Incar conceasion                 | . The normal carry of the refer to internally compendated.                               |
| Pressure input:                       |  |
| · · · · · · · · · · · · · · · · · · · |  |
| Туре                                  | : absolute or gauge  |
|                                       | The pressure values at 4 mA and 20 mA are programmable. Linear                           |
| Span                                  | interpressure values at 4 mA and 20 mA are programmable. Lifted                          |
| Atmoopharia pressure                  | interpolation for all other points.  |
| Atmospheric pressure                  | : If a gauge pressure sensor is used, the atmospheric pressure must be                   |
|                                       | entered.   |
|                                       |  |
|                                       |  |



#### Pulse output:

| Pulse width :<br>Duty cycle :                      | adjustable between 10 ms and 90 ms.   |
|--|---|
| Logic :<br>Current sinking :<br>Pulse generation : | open collector, active low<br>max. 100 mA<br>The pulse count is proportional to the counter difference in selectable<br>units of 10 (1, 10, 100,, 100000) |

#### External keyboard:

| Function | 2 | One input controls the display and one input resets the total counters. |
|----------|---|---|
| Circuit  | : | An input voltage higher than +18 V is detected                          |

#### Communication port:

| Туре         | : | A RS232 interface is provided.<br>Option: RS485 multipoint communication interface for up to 312<br>instruments connected to a common bus. |
|--------------|---|--|
| Baud rate    | 2 | 3009600 Baud   |
| Data bits    | 2 | 7 or 8 selectable  |
| Parity       | 2 | Non, even or odd   |
| Stop bits    | : | 1 or 2 selectable  |
| Data logging | : | Output in intervals up to 9999 minutes or by key stroke.   |

#### Relay output:

| Function     | 1 | High and Low-flow rate alarms based on the flow rate, corrected |
|--------------|---|---|
|              |   | volume, or energy.  |
| Form         | 2 | Normally open (SPST)  |
| Max. voltage | 1 | 250 V AC  |
| Max. current | : | 6 A AC  |

#### Options:

#### Analogue outputs:

| Function    | : | Free selectable: Output current proportional to one of the displayed values. Set points at 0/4 mA and 20 mA, linear interpolation between. |
|-------------|---|--|
| Output span | 2 | 020 mA or 420 mA selectable  |
| Resolution  | 2 | 12 Bit   |
| Max. load   | : | 500 Ω internally powered   |
|             |   | 800 Ω externally 24 V powered  |
| Powering    | : | If there is no external supply >15 V, the output will be internally<br>powered automatically   |

### Control of a sensor-purge-unit:

| Function  | : | Two relays control the solenoid activated valves of a sensor purge unit.<br>During the purging time and an additional selectable time after purging,<br>the flow input is maintained. |
|---|---|---|
| Time between purging<br>Purge duration<br>Time constant |   | 10 minutes to 31 days 23 hours 50 minutes<br>1999 s<br>199 s  |



#### Algorithms:

#### Ideal gases:

| Display<br>Temperature range<br>Pressure range                       | :                | Corrected volume (m³ or SCF), mass (kg or lbs)<br>-273+1000 °C [-460+1832 °F]<br>0100000 kPa <sub>abs</sub> [014514 psi a]   |
|--|------------------|--|
| General Gas:   |                  |  |
| Gases  | :                | Handles most gases where critical temperature, critical pressure and<br>specific gravity are known.  |
| Compressibility<br>Ranges<br><sup>1</sup> Redlich & Quong "An Equati | :<br>:<br>ion of | Calculation using the Redlich-Kwong <sup>1</sup> equation<br>Same as ideal gas.<br>State", Chem Rev., vol. 44, p. 233, 1949  |
| Natural Gas:   |                  |  |
| Gases  | :                | Natural gases with a gross caloric value of 31,8 MJ/m <sup>3</sup> to 38,8 MJ/m <sup>3</sup> , specific gravity ot 0,554 to 0,75, density at reference conditions of 0,716 to 0,970 kg/dm <sup>3</sup> and a and a CO2 and N2 modular fraction of 15 % each. |
| Compressibility  | 1                | Uses the AGA-NX-19-mod equation.   |
|  |                  | -40+115,6 °C [-40+240 °F]  |
| Pressure range   | 1                | 101,325…13,790 kPa <sub>abs</sub> [14,7…2,001 psi a]   |
| Steam:   |                  |  |
| Calculation  | :                | Uses 1967 IFC Formulation (ASME) equations to calculate specific<br>weight and enthalpy of steam.  |
| Steam type   | 1                | Liquid water, saturated and superheated steam  |
| Temperature range  | 1                | 0,01800 °C [32,021472 °F]  |
| Pressure range   | 1                | 0100000 kPa <sub>abs</sub> [014514 psi a]  |
| Saturated steam  | 1                | Either the temperature or pressure input required (not both).  |

# 5 Ordering codes

| Code | Des | escription |  |   |  |  |  |
|------|-----|------------|--|---|--|--|--|
| 515  |     |            | and Steam-Flow-Computer, Type DigiFlow-515 |   |  |  |  |
|      | Ηοι | ising      |  |   |  |  |  |
|      | S   |            |  | mounting IP54 (Standard)                  |  |  |  |
|      | Т   |            |  | mounting with lockable transparent door   |  |  |  |
|      |     | Po         |  | r supply                                  |  |  |  |
|      |     | 2          |  | 0 V AC (Standard)                         |  |  |  |
|      |     | 1          |  | 5 V AC                                    |  |  |  |
|      |     | 4          |  | V AC/DC                                   |  |  |  |
|      |     |            |  | alogue output                             |  |  |  |
|      |     |            | X  | without                                   |  |  |  |
|      |     |            | 1  | One analogue output                       |  |  |  |
|      |     |            | 2  | Two analogue outputs                      |  |  |  |
|      |     |            | 3  | Three analogue outputs                    |  |  |  |
|      |     |            |  | Communication port                        |  |  |  |
|      |     |            |  | 2 RS232 – Serial interface (Standard)     |  |  |  |
|      |     |            |  | 4 RS485 – Multipoint serial interface     |  |  |  |
|      |     |            |  | Sensor-purge-unit                         |  |  |  |
|      |     |            |  | S without relay output                    |  |  |  |
|      |     |            |  | L with relay output for sensor purge unit |  |  |  |
|      |     |            |  |   |  |  |  |
| 515  |     |            |  |   |  |  |  |

www.processteknik.se